

www.emusbms.com

CCGM – Centralized CAN Cell Group Module (CCGM023A)

INTRODUCTION

EMUS Centralized Cell Group Module (CCGM) is a battery cells communication adapter (or "Slave unit") equipped with two CAN connectors for easy BMS system assembly and integrated proprietary EMUS software that allows data transfer within 100ms frequency. CCGM performs all cell data measuring by itself, so the product allows saving space by reducing the need of having cell modules and three-way connectors. CCGM increases the speed of the cell data broadcasting and provides for each connected battery cell balancing functionality.



APPLICATIONS

Any lithium chemistry, series-connected battery pack, or a pack of multiple parallel strings, of up to 512 cells total if using 32 EMUS Centralized CAN Cell Group Modules with connected 16 cells on each. (centralized cell monitoring)


FEATURES


- 2x CAN connectors. Enables communication with CAN equipped EMUS G1 Control Unit and EMUS Centralized Cell Group Modules.
- Supports from 6 up to 16 lithium cells.
- 5x external temperature sensors.
- Using Temperature Breakout (or Extender) board (TBB010A) possible to extend up to 16 temperature
- Balancing of cells, 400mA per each cell.
- Supports 50, 125, 250, 500, 800 kbit/s and 1 Mbit/s CAN baud rates.


MECHANICAL INFORMATION




www.emusbms.com












www.emusbms.com

CONNECTION LAYOUT

Cells Layout: Ext. Temperature Sensors Layout:




Assignment	Mating Housing	Terminal	
(-)			
1+			
2+		43030-0003Molex Micro-latch crimps (recommended crimp tool Molex Hand Crimp Tool P/N: 638190000)	
3+			
4+			
5+			
6+	Microfit 43025-1800 cell connector		
7+			
8+			
9+			
10+			
11+			
12+			
13+			
14+			
15+			
16+			
N/C			
5XGND			
T1		43030-0003 (recommended crimp tool Molex	
T2	Microfit 43025-1000 Temp connector		
Т3		Hand Crimp Tool P/N: 638190000)	
T4			
T5			



www.emusbms.com

CAN Connection Layout:



Assignment	Mating Housing	Terminal
PWR		43030-0003 (recommended crimp tool Molex Hand Crimp Tool P/N: 638190000)
GND	2v minustit /2025 0/00	
CAN_H	2x microfit 43025-0600	
CAN_L		

ELECTRICAL CHARACTERISTICS

Item	Value	
Supply voltage	12-95V	
Supply voltage battery	12.0 VDC to 79.2 VDC (firmware limited by 72.8VDC)	
Power supply reverse protection	yes	
Current consumption	5.6 mA @ 68V - 8.7 mA @ 15V	
Isolation voltage	1000V	
Transient/overvoltage protection between CAN H/CAN L and GND (and vice versa)	24V	
Cell voltage limits	0-4.95V	



www.emusbms.com

OTHER SPECIFICATIONS

Item	Conditions	Value
Call Carret	Other Li chemistries	6-16
Cell Count	LTO cell chemistry	8-16*
CAN Speed		50kbps, 125kbps, 250kbps, 500kbps, 800kbps, 1Mbps (by default 250kbps)
Reserved CAN IDs		0x1FFFFEE5, 0x1FFFFEE6, 0x1FFFE5E5, and 0x1FFFE5E6
Operating Temperature		-40 to +85 °C
IP rating		IP40
Mainh	Without Quick Start Kit	105g
Weight	With Quick Start Kit	145g
Cell communication wire length	In our Quick Start Kit	45cm
Temperature sensors wire length	In our Quick Start Kit	45cm
Call Vallage	General Firmware	2.01 – 4.54V
Cell Voltage	LT0 Firmware	1.01 – 3.54V

INSTALLATION



* Minimum cell count depends on the cell chemistry used. The lowest supported battery pack voltage by internal CCGM parts is 12V, therefore if LTO cells are used then the minimum cell count should be calculated accordingly.

E.g. if LTO cell's expected lowest voltage is 1.5V then the minimum number of cells required would be 8 [12V / 1.5V = 8 cells].

$$V_{BatTotal} \div V_{CellMin} = MinimumNumOfCells$$

NOTE: the absolute minimum total battery pack voltage is 9V, however it is not guaranteed that the device will sense cell voltages correctly.




NOTE: Connection must start from the most negative cell to the most positive. In cases when cells number is less than 16, e.g. 8 cells, then free cells connection wires (dedicated for 9th-16th cells) must ALL be connected to the last 8th (most positive cell).



www.emusbms.com

To setup the 16 cells and 5 external temperature sensors please refer to figure below.

Ext. Temperature Sensors Layout: Cells Layout:



Cells Layout: (using other amount of cells)

